



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Non-Illuminated Rocker

1603M12E

UPC:782116549207

Dimensions:

- **Height:** .982 IN
- **Length:** 1.197 IN
- **Width:** X

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 16A at 125-250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 16(4)A at 250V
- **Circuit Number:** 7
- **Circuit Position Center:** NONE
- **Circuit Position Down:** MOM ON
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Illumination:** Non-illuminated
- **Number Of Poles:** Single-pole
- **Rocker Color:** White
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 1603M12E](#)

Certifications:

- CSA Certified



- UL Recognized

Product compliance:

- RoHS Compliant
- ENEC Marked

© 2016 Eaton. All rights reserved.