



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Rocker

1624-11E

UPC:782116549856

Dimensions:

- **Height:** .982 IN
- **Length:** 1.197 IN
- **Width:** X

Notes:All independent lamps for IP switches to be assembled from terminal positions #24 and #32

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 16A at 125-250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 10(2)A at 250V
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Number Of Poles:** Single-pole
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eaton Specification Sheet - 1624-11E](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- RoHS Compliant
- ENEC Marked



