



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Rocker

1624XA11E

UPC:782116549863

Dimensions:

- **Height:** .982 IN
- **Length:** 1.197 IN
- **Width:** X

Notes:All independent lamps for IP switches to be assembled from terminal positions #24 and #33

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 16A at 125-250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 10(2)A at 250V
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Lamp Voltage:** 125V
- **Lens Color:** Amber
- **Number Of Poles:** Single-pole
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 1624XA11E](#)

Certifications: No Data

Product compliance: No Data



