



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Rocker

250011E

UPC:782116549924

Dimensions:

- **Height:** .982 IN
- **Length:** 1.248 IN
- **Width:** 1.029 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 10(4)A at 250V
- **Circuit Number:** 10
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Number Of Poles:** Two-pole
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 250011E](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- ENEC Marked



- RoHS Compliant