



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Non-illuminated Rocker

250011E734

UPC:782116549955

Dimensions:

- **Height:** .982 IN
- **Length:** 1.248 IN
- **Width:** .595 IN

Notes:Lever depressed toward terminals #13 and #26. Refer to catalog for legend code definitions.

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125V, 10A at 250V, 10A at 28 Vdc
- **Circuit Number:** 10
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Legend Code:** 734
- **Number Of Poles:** Two-pole
- **Rating:** 8A at 14VT
- **Terminals:** 6.3 mm tabs/0.25 in quick connect terminal
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 250011E734](#)



Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data