



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Rocker

2500A11E

UPC:782116550043

Dimensions:

- **Height:** .982 IN
- **Length:** 1.248 IN
- **Width:** 1.029 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 10(4)A at 250V
- **Circuit Number:** 28
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Lamp Voltage:** 125V
- **Number Of Poles:** Two-pole
- **Rocker Color:** Amber
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 2500A11E](#)

Certifications: No Data

Product compliance: No Data



