



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Illuminated Rocker

2500XG11E

UPC:786685681948

Dimensions:

- **Height:** .982 IN
- **Length:** 1.248 IN
- **Width:** .595 IN

Notes:Lever depressed toward terminals #13 and #26.

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Special Features:** Independent lamp
- **Amperage Rating:** 22A at 125V, 16A at 250V, 6A at 125VL, ENEC: 16(4)A 250V
- **Circuit Number:** 28
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Horsepower:** 1 hp at 125-250V
- **Lamp Voltage:** 125V neon
- **Lens Color:** Green
- **Number Of Poles:** Two-pole
- **Rating:** 10A at 14VT
- **Terminals:** 6.3 mm tabs/0.25 in quick connect terminal
- **Throw Type:** Single-throw

Supporting documents:



- [Eaton Specification Sheet - 2500XG11E](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- ENEC Marked

© 2016 Eaton. All rights reserved.