



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CLS type current limiting fuse

2NCLS-25

UPC:786685483313

### Dimensions:

- **Height:** X
- **Length:** 10.8 IN
- **Width:** X

**Notes:** Consult factory for mountings.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** NCLS
- **Voltage Rating:** 2.4 kV
- **Amperage Rating:** 25A
- **Class:** Class R
- **Barrels:** Single barrel
- **Maximum Voltage:** 2.75 kV

### Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 2NCLS-25](#)

### Certifications:

- IEEE Std. C37.41

**Product compliance:** No Data

