



Powering Business Worldwide

pe.eaton.com

CX type current limiting fuse

4CX-25C

UPC:786670500995

Dimensions:

- Height: X
- Length: 10 IN
- Width: X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- Type: CX
- Voltage Rating: 2.4 kV
- Amperage Rating: 25C
- Interrupt Rating: 50 kAIC
- Class: Class C
- Diameter: 1.13 IN
- Barrels: Single barrel
- Maximum Voltage: 4.3 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 4CX-25C](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

