



Powering Business Worldwide

pe.eaton.com

Eaton Navy & Marine complete molded case circuit breaker

504C191G19

UPC:786679559321

Dimensions:

- **Height:** 9.5 IN
- **Length:** 10 IN
- **Width:** 14.5 IN

Weight:21 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 125A
- **Interrupt Rating:** 20 kAIC at 500 Vac, 15 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 500 Vac, 250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Connection:** Front
- **Circuit Breaker Type:** AQB-A250
- **Class:** Naval
- **Magnetic Trip Range:** 1950-3900A at 500 Vac, 2250-4100A at 250 Vdc
- **Frequency Rating:** 400 Hz
- **Trip Rating:** 1950-4100A

Supporting documents:

- [Circuit Breakers Naval Shipboard Use](#)
- [Molded case circuit breakers](#)
- [Eaton Specification Sheet - 504C191G19](#)

Certifications:



- UL Listed

Product compliance:

- MIL-DTL-17361

© 2016 Eaton. All rights reserved.