



Powering Business Worldwide

pe.eaton.com

CXF Type Current Limiting Fuse

5984C66G07

UPC:786685542447

Dimensions:

- **Height:** 2.25 IN
- **Length:** 12.24 IN
- **Width:** 2.25 IN

Weight:2 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CXF
- **Amperage Rating:** 12C
- **Impulse Withstand Voltage:** 95 kV
- **Interrupt Rating:** 50 kA
- **Mounting:** Non-disconnect
- **Maximum Voltage:** 15.5 kV
- **Nominal Voltage:** 14.4 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5984C66G07](#)

Certifications: No Data

Product compliance: No Data

