



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CXF Type Current Limiting Fuse

5984C66G10

UPC:786685542478

### Dimensions:

- **Height:** 2.25 IN
- **Length:** 12.24 IN
- **Width:** 2.25 IN

**Weight:**2 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** CXF
- **Amperage Rating:** 20C
- **Impulse Withstand Voltage:** 95 kV
- **Interrupt Rating:** 50 kA
- **Mounting:** Disconnect
- **Maximum Voltage:** 15.5 kV
- **Nominal Voltage:** 14.4 kV

### Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5984C66G10](#)

**Certifications:** No Data

**Product compliance:** No Data

