



Powering Business Worldwide

pe.eaton.com

Current limiting fuses

5BCLS-24R-Q

UPC:786685882420

Dimensions:

- **Height:** 7 IN
- **Length:** 19.25 IN
- **Width:** 3 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLS
- **Special Features:** Quickship
- **Amperage Rating:** 450A
- **Barrels:** Double-barrel
- **Olr Model Designation:** 24R
- **Maximum Voltage:** 5.08 kV

Supporting documents:

- [Eaton Specification Sheet - 5BCLS-24R-Q](#)

Certifications:

- ANSI/IEEE Std C37.48
- IEEE Std. C37.40
- ANSI/IEEE Std C37.47
- ANSI/IEEE Std C37.48.1
- ANSI/IEEE Std C37.42
- ANSI/IEEE Std C37.41
- IEEE Std. C37.41
- ANSI/IEEE Std C37.46

Product compliance: No Data



