



Powering Business Worldwide

pe.eaton.com

CLS type current limiting fuse

5BCLS-32R

UPC:782116317349

Dimensions:

- **Height:** X
- **Length:** 15.9 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** BCLS
- **Amperage Rating:** 32A
- **Barrels:** Single barrel
- **Mounting:** Bolt-in
- **Class:** R
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 5BCLS-32R](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

