



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CLS type current limiting fuse

**5CLS70-44R**

**UPC:**786670150244

### Dimensions:

- **Height:** X
- **Length:** 15.9 IN
- **Width:** X

**Notes:**Consult factory for mountings.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** CLS
- **Amperage Rating:** 700A
- **Barrels:** Double barrel
- **Diameter:** 4 IN
- **Interrupt Rating:** 50 kA
- **Class:** R
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

### Supporting documents:

- [Medium voltage power fuses](#)
- [Eaton's Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5CLS70-44R](#)

### Certifications:

- IEEE Std. C37.41

**Product compliance:** No Data

