



Powering Business Worldwide

pe.eaton.com

CLS type current limiting fuse

5CLS70-750E

UPC:786670000648

Dimensions:

- **Height:** 7 IN
- **Length:** 32.5 IN
- **Width:** 56.3 IN

Weight:14.7 LB

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLS
- **Amperage Rating:** 750A
- **Barrels:** Double barrel
- **Clip Center:** 12
- **Diameter:** 3 IN
- **Interrupt Rating:** 50 kA
- **Class:** E
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5CLS70-750E](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data



