



Powering Business Worldwide

pe.eaton.com

CME type current limiting fuse

5CME-125E

UPC:786685472102

Dimensions:

- **Height:** X
- **Length:** 17.88 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CME
- **Voltage Rating:** 4.8 kV
- **Amperage Rating:** 125A
- **Class:** Class E
- **Diameter:** 3 IN
- **Barrels:** Single barrel
- **Maximum Voltage:** 5.5 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Multi-range CME and HME fuses](#)
- [Eaton Specification Sheet - 5CME-125E](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

