



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CLS type current limiting fuse

**5MCLS-30-A**

**UPC:**786685409184

### Dimensions:

- **Height:** X
- **Length:** 15.9 IN
- **Width:** X

**Notes:**Consult factory for mountings.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** MCLS
- **Voltage Rating:** 4.8 kV
- **Amperage Rating:** 30A
- **Barrels:** Single barrel
- **Maximum Voltage:** 5.5 kV
- **Prod Size:** Short

### Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5MCLS-30-A](#)

### Certifications:

- IEEE Std. C37.41

**Product compliance:** No Data

