



Powering Business Worldwide

pe.eaton.com

CLS type current limiting fuse

5NCLS-24R

UPC:786685483306

Dimensions:

- **Height:** X
- **Length:** 15.9 IN
- **Width:** X

Notes: Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** NCLS
- **Voltage Rating:** 4.8 kV
- **Amperage Rating:** 24A
- **Class:** Class R
- **Barrels:** Single barrel
- **Maximum Voltage:** 5.5 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 5NCLS-24R](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

