



Powering Business Worldwide

pe.eaton.com

Full Size, Euro-Look Rocker Switches

8004K46N7V2

UPC:786685493619

Dimensions:

- **Height:** 1.602 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Special Features:** Sealed
- **Amperage Rating:** 10A at 250 Vac, 15A at 125 Vac, 15A at 28 Vdc
- **Circuit Position Center:** NONE
- **Circuit Position Down:** 2.1,5.4
- **Circuit Position Up:** 2.3,5.6
- **Frame Color:** Black
- **Illumination:** Non-illuminated
- **Lamp Color:** Clear
- **Mounting:** Snap-in
- **Number Of Poles:** Two-pole
- **Style:** Concave style
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8004K46N7V2](#)



Certifications:

- UL Listed file E2702

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.