



Powering Business Worldwide

pe.eaton.com

Full Size Euro-Look Rocker Switches

8004K61N1V2

UPC:786685677811

Dimensions:

- **Height:** 1.602 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Type:** Sealed
- **Amperage Rating:** 15A at 125V, 10A at 250V, 15A at 28 Vdc
- **Circuit Position Center:** 5.3
- **Circuit Position Down:** 5.1
- **Circuit Position Up:** 5.6
- **Frame Color:** Black
- **Horsepower:** 0.25 hp at 125-250V
- **Illumination:** Non-illuminated
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Two-pole
- **Style:** Two-face
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8004K61N1V2](#)



Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.