



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Full Size Euro-Look Rocker Switches

8004K61N7V1

UPC:786685677828

### Dimensions:

- **Height:** 1.602 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

### Specifications:

- **Type:** Non-sealed
- **Amperage Rating:** 15A at 125V, 10A at 250V, 15A at 28 Vdc
- **Circuit Position Center:** 5.3
- **Circuit Position Down:** 5.1
- **Circuit Position Up:** 5.6
- **Frame Color:** Black
- **Horsepower:** 0.25 hp at 125-250V
- **Illumination:** Non-illuminated
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Two-pole
- **Style:** Concave
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8004K61N7V1](#)



**Certifications:**

- UL Recognized
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.