



Powering Business Worldwide

pe.eaton.com

Full Size Euro-Look Illuminated Rocker Switches

8005K20N319V62

UPC:786685677903

Dimensions:

- **Height:** 1.602 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Notes: 15 Vdc and 28 Vdc bulbs are not UL, CSA when bulb is wired dependent to switch circuit. All double-throw circuits, both 1PDT and 2PDT are provided with two lamps and two lenses when lamp wired dependent to circuit.

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Special Features:** Dependent wiring
- **Type:** Sealed
- **Amperage Rating:** 15A at 125V, 10A at 250V, 15A at 28 Vdc
- **Circuit Position Center:** OFF
- **Circuit Position Down:** 2.1
- **Circuit Position Up:** 2.3
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Lamp Color:** Clear
- **Lamp Voltage:** 14 Vdc
- **Lens Color:** Blue
- **Mounting:** Snap-in mounting
- **Number Of Lenses:** Two lens
- **Number Of Poles:** Single-pole



- **Style:** Concave
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8005K20N319V62](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data