



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## EURO SR Standard Size Euro-Style Rocker Switches

8006K25N1M2

UPC:782116552856

### Dimensions:

- **Height:** 1.082 IN
- **Length:** 1.705 IN
- **Width:** .957 IN

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

### Specifications:

- **Special Features:** Sealed
- **Amperage Rating:** 10A at 250 Vac, 15A at 125 Vac, 15A at 28 Vdc
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** 2.3
- **Frame Color:** Black
- **Illumination:** Non-illuminated
- **Lamp Color:** Clear
- **Lens Color:** Red
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Rocker Color:** White
- **Style:** Two face rocker style
- **Terminals:** Screw terminals
- **Texture:** Matte
- **Throw Type:** Single-throw

### Supporting documents:

- [Eaton's Volume 11-Vehicle and Commercial Controls](#)



- [Eaton Specification Sheet - 8006K25N1M2](#)

**Certifications:**

- UL Listed file E2702

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.