



Powering Business Worldwide

pe.eaton.com

EURO SR Standard Size Euro-Style Rocker Switches

8006K60N1M2

UPC:786680127397

Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

Weight:8 LB

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Type:** Sealed
- **Amperage Rating:** 10A at 250V, 15A at 125V, 15A at 28 Vdc
- **Circuit Position Center:** 5.6
- **Circuit Position Down:** OFF
- **Circuit Position Up:** 2.3, 5.6
- **Frame Color:** Black
- **Illumination:** Non-illuminated
- **Mounting:** Standard
- **Number Of Poles:** Two-pole
- **Rocker Color:** White
- **Style:** Two-face
- **Terminals:** Screw
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)



- [Eaton Specification Sheet - 8006K60N1M2](#)

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.