



Powering Business Worldwide

pe.eaton.com

EURO SR Standard Size Euro-Style Rocker Switches

8007K23N113V22

UPC:782116571772

Dimensions:

- **Height:** 1.082 IN
- **Length:** 1.705 IN
- **Width:** .957 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Special Features:** Sealed
- **Amperage Rating:** 10A at 250 Vac, 15A at 125 Vac, 15A at 28 Vdc
- **Circuit Position Center:** NONE
- **Circuit Position Down:** 2.1
- **Circuit Position Up:** OFF
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Lamp Color:** Clear
- **Lamp Voltage:** 125V
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Two face rocker style
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Single-throw
- **Wiring Connection:** Dependent

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)



- [Eaton Specification Sheet - 8007K23N113V22](#)

Certifications:

- UL Listed file E2702

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.