



Powering Business Worldwide

pe.eaton.com

EURO SR Standard Size Illuminated Rocker Switches

8007K23N413V52

UPC:786685949185

Dimensions:

- **Height:** 1.98 IN
- **Length:** 1.71 IN
- **Width:** .95 IN

Weight:.045 LB

Notes:15 Vdc and 28 Vdc bulbs are not UL, CSA when bulb is wired dependent to switch circuit. All double-throw circuits, both 1PDT and 2PDT are provided with two lamps and two lenses when lamp wired dependent to circuit.

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Type:** Sealed
- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Circuit Position Center:** NONE
- **Circuit Position Down:** 2.1
- **Circuit Position Up:** OFF
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Lamp Color:** Clear
- **Lamp Voltage:** 28 Vdc
- **Mounting:** Snap-in mounting
- **Number Of Lenses:** No lens
- **Number Of Poles:** Single-pole
- **Style:** Two-face
- **Terminals:** 0.250 in spade terminal



- **Texture:** Matte
- **Throw Type:** Single-throw

Supporting documents:

- [Eaton Specification Sheet - 8007K23N413V52](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance:

- Not Applicable