



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## AC Rated Standard Rockette Switches

**8138K20E6M52**

**UPC:**786685681450

### Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

**Weight:**9 LB

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

### Specifications:

- **Amperage Rating:** 6A at 125V, 3A at 250V, 2A at 277V
- **Circuit Number:** D
- **Circuit Position Center:** OFF
- **Circuit Position Down:** MOM ON
- **Mounting:** Standard mounting (m)
- **Number Of Poles:** Two-pole
- **Rocker Color:** White
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8138K20E6M52](#)

### Certifications:

- UL Recognized
- CSA Certified



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.