



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## AC Rated Standard Rockette Switches

8142K20Z7V52

UPC:786685677118

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

### Specifications:

- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Circuit Number:** D
- **Circuit Position Center:** OFF
- **Circuit Position Down:** 2.1
- **Circuit Position Up:** 2.3
- **Horsepower:** 0.75 hp at 250V
- **Mounting:** Snap-in mounting (z)
- **Number Of Poles:** Two-pole
- **Rocker Color:** Black
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8142K20Z7V52](#)

### Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data



