



Powering Business Worldwide

pe.eaton.com

AC Rated Standard Rockette Switches

8142K22Z37V50

UPC:786685679884

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Circuit Number:** D
- **Circuit Position Center:** NONE
- **Circuit Position Down:** ON
- **Horsepower:** 0.75 hp at 250V
- **Mounting:** Snap-in mounting (z)
- **Number Of Poles:** Two-pole
- **Rocker Color:** Black
- **Terminals:** Screw terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8142K22Z37V50](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data



