



Powering Business Worldwide

pe.eaton.com

AC Rated Standard Rockette Switches

8148K20E7M52

UPC:786685681733

Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

Weight:9 LB

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Circuit Number:** D
- **Circuit Position Center:** OFF
- **Circuit Position Down:** MOM ON
- **Horsepower:** 0.75 hp at 250V
- **Mounting:** Standard mounting (m)
- **Number Of Poles:** Two-pole
- **Rocker Color:** White
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8148K20E7M52](#)

Certifications:

- UL Recognized
- CSA Certified



Product compliance: No Data

© 2016 Eaton. All rights reserved.