

Eaton Navy & Marine complete molded case circuit breaker

83E3554

UPC:782116071289

Dimensions:

- **Height:** 5.8 IN
- **Length:** 7.25 IN
- **Width:** 5.8 IN

Weight:6.2 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 15A
- **Interrupt Rating:** 15 kAIC at 500 Vac, 10 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 500 Vac, 250 Vdc
- **Trip Type:** Thermal-magnetic
- **Circuit Breaker Type:** AQB-A101
- **Class:** Naval
- **Auxiliary Switch:** 2A-2B
- **Magnetic Trip Range:** 180-210A at high setting, 75-105A at low setting
- **Frequency Rating:** 60 Hz
- **Trip Rating:** 75-210A hi, 75-105A low

Supporting documents:

- [Molded case circuit breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 83E3554](#)

Certifications: No Data

Product compliance:

- MIL-DTL-17361

© 2016 Eaton. All rights reserved.