



Powering Business Worldwide

pe.eaton.com

CLT type current limiting fuse

8CLT-12

UPC:786670222842

Dimensions:

- **Height:** X
- **Length:** 9.7 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLT
- **Voltage Rating:** 7.2 kV
- **Amperage Rating:** 12A
- **Interrupt Rating:** 25 kAIC
- **Diameter:** 1.6 IN
- **Barrels:** Single barrel
- **Maximum Voltage:** 8.3 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 14-Fuses](#)
- [Eaton Specification Sheet - 8CLT-12](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

