



Powering Business Worldwide

pe.eaton.com

CX type current limiting fuse

8CXI-25C

UPC:786685408262

Dimensions:

- **Height:** X
- **Length:** 10 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CXI
- **Voltage Rating:** 7.2 kV
- **Amperage Rating:** 25C
- **Interrupt Rating:** 50 kAIC
- **Class:** Class C
- **Diameter:** 2 IN
- **Barrels:** Single barrel
- **Maximum Voltage:** 8.3 kV

Supporting documents:

- [Medium voltage power fuses](#)
- [Eaton's Volume 14-Fuses](#)
- [Eaton Specification Sheet - 8CXI-25C](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

