

Eaton definite purpose starter

A27SNC15T001

UPC:782116915002

Dimensions:

- **Height:** 5.5 IN
- **Length:** 3.7 IN
- **Width:** 2.4 IN

Weight:1.6 LB

Warranties:

- 1 year

Specifications:

- **Model:** Starter
- **Amperage Rating:** 15A
- **Coil:** Coil: 24 V, 50/60 Hz
- **Control Characteristics:** Separate control wiring
- **Enclosure:** Open with metal mounting plate
- **Inductive Full Load:** 15 A IFL
- **Phase:** Three-phase
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing
- **Overload Relay:** 0.6-1 FLA

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A27SNC15T001](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

