



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2430L125G

UPC:782116139293

Dimensions:

- **Height:** 27 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:Ground bar is installed

Warranties:

- 10 year

Specifications:

- **Special Features:** Ground bar
- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** G1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BW
- **Mounting:** Combination
- **Number Of Circuits:** 30
- **Number Of Spaces:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #2/0-300 kcmil Cu/Al at 60°C or 75°C

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR2430L125G

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.