



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR Style 1 in Loadcenter

**BR3042L125**

**UPC:**786685857060

### Dimensions:

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

**Weight:**10 LB

### Warranties:

- 10 year

### Specifications:

- **Type:** Split neutral
- **Amperage Rating:** 125A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Number Of Circuits:** 42
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #6-2/0 Cu/Al at 60°C or 75°C
- **Accessories:** BREQS125 hold-down screw
- **Used With:** Type BR 1 in breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3042L125](#)



**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.