

## Eaton BR main breaker loadcenter

**BR4040B200ENCL**

**UPC:**782116347193

### **Dimensions:**

- **Height:** 40.75 IN
- **Length:** 4.5 IN
- **Width:** 16 IN

**Weight:**39.36 LB

**Notes:**Enclosure only for a br4040b200- neutrals installed

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Type:** Main circuit breaker loadcenter enclosure
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 40
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

**Supporting documents:**



- [Loadcenters and Circuit Breakers](#)
- [Eaton Specification Sheet - BR4040B200ENCL](#)

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.