

Eaton BR main breaker loadcenter

BR4040BC200VCA2

UPC:786685290775

Dimensions:

- **Height:** 41.5 IN
- **Length:** 4.5 IN
- **Width:** 16 IN

Weight:45 LB

Notes:Includes 5-br120, 1-br230, 2-br120cafa

Warranties:

- 10 year

Specifications:

- **Special Features:** Value Pack w / (2) BRCAF120, (5) BR120, (1) BR230
- **Type:** Main circuit breaker loadcenter
- **Amperage Rating:** 200A
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 40
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eaton Specification Sheet - BR4040BC200VCA2](#)

Certifications:

- UL 50
- UL 67



Product compliance: No Data

© 2016 Eaton. All rights reserved.