

Eaton CPX9000 Clean power drive

CPX02564EAK4L1P1

UPC:782116941780

Dimensions:

- **Height:** 90 IN
- **Length:** 28.05 IN
- **Width:** 21.5 IN

Weight:800 LB

Notes:Brake chopper is standard in drives up to 30hp or 40hp at 480V, it is optional in larger drives. Some options are voltage and/or hp specific, consult your Eaton rep for details.

Warranties:

- 2 year

Specifications:

- **Display:** Power, RUN and fault pilot lights
- **Input:** Input Disconnect
- **Application:** IH/internal brake chopper
- **Control Characteristics:** HAND/OFF/AUTO switch .87 in
- **Enclosure:** 7
- **Frame Size:** FR6
- **Horsepower:** 25 hp
- **Style:** Enclosed drive
- **Type:** Type 12 filtered
- **Voltage Rating:** 480 V

Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Eaton's Volume 6-Solid-State Motor Control](#)
- [CPX9000 clean power drives in MCCs - the best solution for clean power](#)
- [Eaton Specification Sheet - CPX02564EAK4L1P1](#)

Certifications:

- UL 508C

Product compliance: No Data

© 2016 Eaton. All rights reserved.