

## Eaton CPX9000 Clean power drive

**CPX04014BAK4P1**

**UPC:**782116944002

### **Dimensions:**

- **Height:** 90 IN
- **Length:** 28.05 IN
- **Width:** 21.5 IN

**Weight:**800 LB

**Notes:**Brake chopper is standard in drives up to 30hp or 40hp at 480V, it is optional in larger drives. Some options are voltage and/or hp specific, consult your Eaton rep for details.

### **Warranties:**

- 2 year

### **Specifications:**

- **Input:** Input Disconnect
- **Application:** IL/internal brake chopper
- **Control Characteristics:** HAND/OFF/AUTO switch .87 in
- **Enclosure:** 7
- **Frame Size:** FR6
- **Horsepower:** 40 hp
- **Style:** Enclosed drive
- **Type:** Type 1
- **Voltage Rating:** 480 V

### **Supporting documents:**

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [CPX9000 clean power drives in MCCs - the best solution for clean power](#)
- [Eaton Specification Sheet - CPX04014BAK4P1](#)

### **Certifications:**

- UL 508C

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.