



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CPX Enclosed Drives

**CPX07564AAK4L1**

**UPC:**782116944682

### Dimensions:

- **Height:** 90 IN
- **Length:** 28.05 IN
- **Width:** 21.5 IN

**Weight:**1000 LB

**Notes:** Brake chopper is standard in drives up to 30hp or 40hp at 480V, it is optional in larger drives. Some options are voltage and/or hp specific, consult your Eaton rep for details.

### Warranties:

- 2 year

### Specifications:

- **Display:** Power, RUN and fault pilot lights
- **Application:** IL/no brake chopper
- **Control Characteristics:** HAND/OFF/AUTO switch .87 in
- **Enclosure:** 7
- **Frame Size:** FR7
- **Horsepower:** 75 hp
- **Style:** Enclosed drive
- **Type:** Type 12 filtered
- **Voltage Rating:** 480V

### Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [CPX9000 clean power drives in MCCs - the best solution for clean power](#)
- [Eaton Specification Sheet - CPX07564AAK4L1](#)

### Certifications:

- UL 508C

**Product compliance:** No Data



