



Powering Business Worldwide

pe.eaton.com

CPX Enclosed Drives

CPX10064AA

UPC:782116944866

Dimensions:

- **Height:** 90 IN
- **Length:** 28.05 IN
- **Width:** 21.5 IN

Weight:1400 LB

Notes: Brake chopper is standard in drives up to 30hp or 40hp at 480V, it is optional in larger drives. Some options are voltage and/or hp specific, consult your Eaton rep for details.

Warranties:

- 2 year

Specifications:

- **Application:** IL/no brake chopper
- **Enclosure:** 7
- **Frame Size:** FR8
- **Horsepower:** 100 hp
- **Style:** Enclosed drive
- **Type:** Type 12 filtered
- **Voltage Rating:** 480V

Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [CPX9000 clean power drives in MCCs - the best solution for clean power](#)
- [Eaton Specification Sheet - CPX10064AA](#)

Certifications:

- UL 508C

Product compliance: No Data



