

Eaton heavy duty single-throw fused safety switch

DH463FDKCB

UPC:782116631247

Dimensions:

- **Height:** 24.95 IN
- **Length:** 15.1 IN
- **Width:** 10.22 IN

Weight: .01 LB

Notes: Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Cube fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Four-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 50 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 60 at 480 Vac TD 3 Ph, 75 at 600 Vac TD 3 Ph

Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)



- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH463FDKCB](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.