



Powering Business Worldwide

pe.eaton.com

Series C, F-frame Molded Case Mining Circuit Breaker

E2FM150UM

UPC:786679064474

Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

Weight:4.5 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Specialty sealed
- **Amperage Rating:** 150A
- **Interrupt Rating:** 65 kAIC at 240V, 25 kAIC at 480V, 18 kAIC at 600V, 10 kAIC at 1000Y/577, 10 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 250 Vdc
- **Frame Size:** F-frame
- **Magnetic Trip Range:** 750-2500A
- **Maximum Voltage:** 1000Y/577V
- **Series:** Series C
- **Terminals:** Line and load
- **Trip Type:** Non-interchangeable magnetic

Supporting documents:

- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - E2FM150UM](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.