

## Eaton E57 inductive proximity sensor

**E57EBL12T110**

**UPC:**782114152812

### **Dimensions:**

- **Height:** 1.18 IN
- **Length:** .47 IN
- **Width:** .47 IN

**Weight:**.04 LB

### **Warranties:**

- 1 year

### **Specifications:**

- **Accuracy:** < 1%
- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Contact Rating:** 200 mA at 30 Vdc
- **Contact Configuration:** NPN Open Collector, Normally Closed
- **Cord Length:** 79.2 FT
- **Diameter:** .47 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 200 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity
- **Series:** E57

### **Supporting documents:**

- [Eaton Specification Sheet - E57EBL12T110](#)

### **Certifications:**

- UL Listed
- CSA Certified

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.