

Eaton C30CN mechanically held lighting contactor

ECC03C1TAA-P8P23P25

UPC:782116155279

Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

Weight:13 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Accessories:** ON/OFF pushbutton, red RUN pilot light, green OFF pilot light
- **Amperage Rating:** 30A
- **Coil Voltage:** 24V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Ten-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECC03C1TAA-P8P23P25](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data



