

Eaton C30CN mechanically held lighting contactor

ECC04C1H2A-S3P23

UPC:782116155866

Dimensions:

- **Height:** 13.21 IN
- **Length:** 7.73 IN
- **Width:** 5.84 IN

Weight:13.5 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Accessories:** HAND/OFF/AUTO selector switch, red RUN pilot light
- **Amperage Rating:** 30A
- **Coil Voltage:** 277V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Two-pole
- **Type:** Non-combination mechanically held and magnetically latched

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECC04C1H2A-S3P23](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data



