

Eaton CN35 electrically held lighting contactor

ECL03E1E3A

UPC:782114082928

Dimensions:

- **Height:** 26.51 IN
- **Length:** 8.03 IN
- **Width:** 11.66 IN

Weight:39 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 100A
- **Coil Voltage:** 208V/60 Hz
- **Contact Rating:** 100 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 90 mm
- **Number Of Poles:** Three-pole
- **Operation:** Electrically held
- **Series:** A202 Series
- **Type:** Non-combination electrically held

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL03E1E3A](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data



