

Eaton CN35 electrically held lighting contactor

ECL03F1A2A-S3

UPC:786685399287

Dimensions:

- **Height:** 28.313 IN
- **Length:** 13.188 IN
- **Width:** 11.563 IN

Weight:41 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Accessories:** HAND/OFF/AUTO selector switch
- **Amperage Rating:** 200A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Contact Rating:** 200 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 180 mm
- **Number Of Poles:** Two-pole
- **Operation:** Electrically held
- **Series:** A202 Series
- **Type:** Non-combination electrically held

Supporting documents:

- [Lighting contactors](#)
- [Eaton's Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL03F1A2A-S3](#)

Certifications:

- cUL Listed
- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.